



## Scattering Meter Calibration Sheet

4/21/2016

Wavelength: 470

S/N BB2FLMBC-1429

Use the following equation to obtain "scaled" output values:

$$\beta(\theta_c) \text{ m}^{-1} \text{ sr}^{-1} = \text{Scale Factor} \times (\text{Output} - \text{Dark Counts})$$

- **Scale Factor for 470 nm** = 1.098E-05 (m<sup>-1</sup>sr<sup>-1</sup>)/counts
- **Output** = meter reading counts
- **Dark Counts** = 52 counts

Instrument Resolution = 1.2 counts 1.33E-05 (m<sup>-1</sup>sr<sup>-1</sup>)

### Definitions:

- **Scale Factor:** Calibration scale factor,  $\beta(\theta_c)/\text{counts}$ . Refer to User's Guide for derivation.
- **Output:** Measured signal output of the scattering meter.
- **Dark Counts:** Signal obtained by covering detector with black tape and submersing sensor in water.

Instrument Resolution: Standard deviation of 1 minute of collected data.