

PO Box 518
620 Applegate St.
Philomath, OR 97370



(541) 929-5650
Fax (541) 929-5277
www.Seabird.com

Scattering Meter Calibration Sheet

1/0/1900

Wavelength: 470

S/N BB2FLMBC-5949

Use the following equation to obtain "scaled" output values:

$$\beta(\theta_c) \text{ m}^{-1} \text{ sr}^{-1} = \text{Scale Factor} \times (\text{Output} - \text{Dark Counts})$$

- **Scale Factor for 470 nm** = 1.133E-05 (m⁻¹sr⁻¹)/counts
- **Output** = meter reading counts
- **Dark Counts** = 53 counts

Instrument Resolution = 1.0 counts 1.13E-05 (m⁻¹sr⁻¹)

Definitions:

- **Scale Factor:** Calibration scale factor, $\beta(\theta_c)/\text{counts}$. Refer to User's Guide for derivation.
- **Output:** Measured signal output of the scattering meter.
- **Dark Counts:** Signal obtained by covering detector with black tape and submersing sensor in water.

Instrument Resolution: Standard deviation of 1 minute of collected data.